

Improved nVent CADDY Cat HP J-Hook Mod Clip with Rod/Wire Clip



Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

CERTIFICATIONS




VLASTNOSTI

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY

SPECIFIKACE

Table 1/1						
Katalogové číslo	Article Number	Povrchová úprava	Materiál	Rod Size (RS)	Velikost drátu	Static Load
CATHPM4Z34	186082	nVent CADDY Armour	Spring Steel	M4, M6, M8, M10, M12	4.8 - 6.4 mm	130N



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte

