

Metal Pressure Clip with Nail Gun Insert



VLASTNOSTI

Clips onto nozzle of gas or battery-actuated nail guns allowing for hands-off installation at structure or from the floor using a pole

Ideal for smaller runs of cables

Flexible clip retains shape and allows for cables to be inserted after installation

Rounded edges help prevent cable damage

Cables are neatly installed providing a consistent and professional appearance

Low profile allows for installations in tight spaces

SPECIFIKACE

Povrchová úprava: nVent CADDY Armour

Materiál: Spring Steel;Nylon

Table 1/1

Katalogové číslo	Article Number	Cable Capacity	Diameter (Ø)	Hole Size (HS)	Length (L)
PKM16H3GBSF	182054	16	10 mm	3 mm	233.5mm
PKM10H3GBSF	182053	10	10 mm	3 mm	171.5mm

DALŠÍ PODROBNOSTI O PRODUKTU

Supports cable diameters up to 1/2" (13 mm) when installed with a standard 1/4" (6 mm) washer.

Nail gun insert is compatible with BeA® CN60-688ES, Hilti® BX 3, GX 3, DEWALT® Trak-It C3, SPIT® PULSA 40E, 800E, 700, 1000 or equivalent nailers.

Please consult with the nail manufacturer to evaluate the static load of the nail and type of concrete used for the installation.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

