

# nVent CADDY Pyramid Tool-Free Pipe Clamp



## VLASTNOSTI

Push-in clamps install without the need for additional tools or strut clamps

Clamps come in two different sizes to fit project needs

Plastic clamps and base will not corrode pipe

## SPECIFIKACE

**Materiál:** Nylon  
**Temperature:** -45 to 65 °C

Table 1/1

| Katalogové číslo | Article Number | Outer Diameter (OD) | Length (L) | Width (W) | A      | Unit Weight |
|------------------|----------------|---------------------|------------|-----------|--------|-------------|
| PTF1C            | 360484         | 12.7 - 22.4 mm      | 40.6mm     | 19.1 mm   | 9.5 mm | 0.01 kg     |
| PTF2C            | 360485         | 21.3 - 60.3 mm      | 81.3mm     | 19.1 mm   | 9.5 mm | 0.02 kg     |

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte

