

# nVent CADDY Single-Arm Cable Pressure Clip



The nVent CADDY Single-Arm Cable Pressure Clip is a sustainable, ready-to-install metal clip allowing for easy cable installation with one hand. This solution securely supports small-sized cable bundles in crowded spaces—such as flush to ceilings, above suspended ceilings. The Single-Arm Pressure Clip’s unique design creates an option to combine two single-arm clips within seconds—ultimately doubling the cable capacity per a single fixing point, reducing the number of required stock parts, and saving contractors time on the job. Featuring a low-profile design, this cable pressure clip is a more durable alternative to commonly used plastic solutions and offers an ideal solution for electrical and datacom applications.

## VLASTNOSTI

Gangable/Two-in-one solution; two nVent CADDY Single-Arm Cable Pressure Clips can be combined by hand to instantly double the cable capacity per single fixing point

Compatible with direct fastening and traditional anchoring

Reusable in case of nail misfire

More robust and durable than plastic pressure clips

Rounded edges help prevent cable damage

Cables are neatly installed, providing a consistent and professional appearance

Low-profile design allows for installation in tight spaces

Made of 100% recyclable materials

## SPECIFIKACE

**Povrchová úprava:** Pregalvanized

**Materiál:** Ocel

Table 1/2

| Katalogové číslo | Article Number | Hole Size (HS) | Length (L) | Výška (H) | Šířka (W) | Diameter 1 (Ø1) |
|------------------|----------------|----------------|------------|-----------|-----------|-----------------|
| OAB8DF           | 182068         | 4.8 mm         | 115mm      | 15mm      | 30mm      | 4 - 10 mm       |

| Katalogové číslo | Article Number | Hole Size (HS) | Length (L) | Výška (H) | Šířka (W) | Diameter 1(Ø1) |
|------------------|----------------|----------------|------------|-----------|-----------|----------------|
| OAB8             | 182067         | 7.5 mm         | 115mm      | 15mm      | 30mm      | 4 - 10 mm      |



Table 2/2

| Katalogové číslo | Article Number | Diameter 2 (Ø2) | Cable Capacity |
|------------------|----------------|-----------------|----------------|
| OAB8DF           | 182068         | 5 - 11 mm       | 8              |
| OAB8             | 182067         | 5 - 11 mm       | 8              |

## DALŠÍ PODROBNOSTI O PRODUKTU

\*Cable capacity based on a 10mm diameter cable

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

