

Telescopic Screw Gun Box Strap



The nVent CADDY Telescopic Screw Gun Box Strap is a versatile and robust support inspired by installers in the UK to securely fasten electric boxes to in-wall studs. Its engineered profile guarantees an extra sturdy and durable connection to the box and studs while requiring a minimal amount of screws. Available in two sizes, the box strap accommodates most stud spacings without cumbersome and time-consuming rework.

VLASTNOSTI

Engineered profile with a recessed cavity to provide extra sturdy connection to the box and prevent loosening over time, even with short 12 mm-long self-tapping screws

Improved design only requires a single screw per tab and two screws per box, saving up to 30% of installation time

Can mount multiple boxes

Notched and marked for easy identification and bending, tailored to UK market box depths

Improved design with stamped mm markings and pilot holes accelerates precise box conduit mounting between studs

V cut-out and line of pilot holes indicates a bar's center for a fast bracket leveling using a laser level

Pilot holes allow easy box attachment with a screwdriver

Requires only a screw gun to install

Can be mounted to face or inside of stud using a single screw per tab

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly

Unique, one-piece, break apart design

SPECIFIKACE

Povrchová úprava: Pregalvanized

Materiál: Ocel

Table 1/1

Katalogové číslo	Article Number	Stud Spacing	Box Depth
TSGB1624UK	187202	355 - 655 mm	25mm, 35mm, 47mm

Katalogové číslo	Article Number	Stud Spacing	Box Depth
TSGB812UK	187201	200 - 350 mm	25mm, 35mm, 47mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

