


Electrical Earth Bar, Tinned, 16 Connections, 0 Number of Disconnects, 950 mm

Data Solutions

KATALOGOVÉ ČÍSLO

EEB16T506D0A



VLASTNOSTI

Provides a convenient, single-point grounding and bonding location

Busbars with disconnect links allow for convenient testing of the earth termination system

High conductivity, hard drawn, electrolytic tough pitch copper per EN 13601

Includes halogen-free polyamide insulators, stainless steel (EN 1.4401) hardware and mounting brackets

Custom bars can be designed and manufactured to customer specifications

VLASTNOSTI PRODUKTU

Complies With: IEC® EN 62561-1:2017 Class H

Materiál: Copper

Povrchová úprava: Tinned

Number of Connections: 16

Number of Disconnects: 0

Thread Size (TS): M10

Height (H): 94mm

Length (L): 950mm

Width 1 (W1): 100mm

Width 2 (W2): 50mm

Thickness (T): 6mm


A: 50mm

Unit Weight: 4.21kg

DALŠÍ PODROBNOSTI O PRODUKTU

Tinned finish is 8 microns according to ASTM B545 Service Class "C" for corrosive environments.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE