

Cable to Web of Rail Mold Only, Signal, Field-made Bond Terminal Style, 50 mm² Solid, Right Hand

Data Solutions

KATALOGOVÉ ČÍSLO

SBWW6RH



VLASTNOSTI

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

VLASTNOSTI PRODUKTU

Materiál: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: Field-made

Conductor Size: 50 mm² Solid

Conductor Outer Diameter, Nominal: 8mm

Welder Style: T21

Orientation: Right Hand

Mold Only: Yes

Welding Material: SB32 or SB25PLUSF80, Sold Separately

Handle Clamp: C105B, Sold Separately

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE