

Varistar CP Double Steel Door, Perforated, 3-Point Locking, RAL 7021, 38 U, 1800H, 800W

Data Solutions

KATALOGOVÉ ČÍSLO

21630-455



Perforated Varistar CP steel double door with 3-point locking for applications with IP 20 protection

VLASTNOSTI

Double perforated steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

VLASTNOSTI PRODUKTU

Rack Height: 38U

Výška: 1800mm

Šířka: 800mm

Množství v balení: 1

Barva: Black Grey

Kód barvy: RAL 7021

Complies With: IEC 61587-1; IEC 61587-3

Povrchová úprava: Strukturovaný Práškový

Locking Type: 3-Point Locking

Materiál: Ocel

Produktová řada: Varistar CP

Product Type: Cabinet Door

Stupeň krytí: IP20

Typ: Steel Double Door, Perforated

Works With: Varistar CP

Net Weight: 18.202kg

DALŠÍ PODROBNOSTI O PRODUKTU

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE