

Socket Strip, IEC C13, With Wieland® Input

Data Solutions



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



VLASTNOSTI

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPECIFIKACE

Length:	438.5mm
Materiál:	Hliník; Polyamide
Product Type:	Socket Strip

Table 1/2

Katalogové číslo	Typ zásuvky	Socket Quantity	Switched Outlets	Napětí střídavé	Function	Množství v balení
60110-340	IEC C13	12	No	230V		1
60110-341	IEC C13	12	No	230V		1
60110-342	IEC C13	12	No	230V		1
60110-349	IEC C13	6	No	230V	Overcurrent Protection	1
60110-350	IEC C13	6	No	230V	Overcurrent Protection	1
60110-351	IEC C13	6	No	230V	Overcurrent Protection	1

Table 2/2

Katalogové číslo	Barva	Hloubka	Povrchová úprava
60110-340	Grey	44mm	Anodized
60110-341	Black	44mm	Anodized
60110-342	Red	44mm	Anodized
60110-349	Grey	44mm	Anodized
60110-350	Black	44mm	Anodized
60110-351	Red	44mm	Anodized

DALŠÍ PODROBNOSTI O PRODUKTU

Please order mounting bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE