

Special Track Work Mold Only, Power

Data Solutions



VLASTNOSTI

Replacement molds designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

SPECIFIKACE

Rail Type: Crane Rail Profiles

Materiál: Graphite

Bond Terminal Style: J

Table 1/1

Katalogové číslo	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT503RHM	2/0 Concentric	10.62mm	T5	Right Hand
PBJT503LHM	2/0 Concentric	10.62mm	T5	Left Hand
PBJT52QM	4/0 Concentric	13.41mm	T5	Left and Right Hand
PBJT52QRHM	4/0 Concentric	13.41mm	T5	Right Hand

Katalogové číslo	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBJT52QLHM	4/0 Concentric	13.41mm	T5	Left Hand
PBJT52WM	250 kcmil Ropelay	19.05mm	T5	Left and Right Hand
PBJT52WRHM	250 kcmil Ropelay	19.05mm	T5	Right Hand
PBJT52WLHM	250 kcmil Ropelay	19.05mm	T5	Left Hand

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE