

Telescopic Slides C-Profile for Cabinet

Data Solutions



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

CERTIFICATIONS



VLASTNOSTI

For mounting 84 HP wide subracks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the subrack (it is inserted into the guiding profile like a telescopic slide)

SPECIFIKACE

Materiál:	Hliník
Povrchová úprava:	Anodized
Typ:	C Profile
Product Type:	Telescopic Slide

Table 1/1

Katalogové číslo	Hloubka	Množství v balení
------------------	---------	-------------------

24562-446	250mm	2
24562-460	500mm	2
24562-464	600mm	2
24562-449	600mm	2
24562-461	600mm	2
24562-466	800mm	2
24562-451	800mm	2
24562-474	800mm	2
24562-467	900mm	2
24562-452	900mm	2
24562-468	1000mm	2
24562-472	1100mm	2
24562-473	1200mm	2

DALŠÍ PODROBNOSTI O PRODUKTU

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE