

Cable to Web of Rail Mold Only, Signal



VLASTNOSTI

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

SPECIFIKACE

Rail Type: 85 lb to 141 lb T-Rail Sections

Materiál: Graphite

Table 1/1

Katalogové číslo	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
SBB200CLH	1" Tab	3/16" Bondstrand	4.76mm	TB5, T21	Left Hand
SBB200CRH	1" Tab	3/16" Bondstrand	4.76mm	TB5, T21	Right Hand
SBW3150BLH	1" Tab	3/16" Bondstrand	4.76mm	TB5	Left Hand
SBW3150BRH	1" Tab	3/16" Bondstrand	4.76mm	TB5	Right Hand
SBB200YLH	1" Tab	16 mm ² Concentric	5.18mm	T21, TB5	Left Hand
SBB200YRH	1" Tab	16 mm ² Concentric	5.18mm	T21, TB5	Right Hand

Katalogové číslo	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
SBB200XRH	1" Tab	25 mm ² Stranded	6.6mm	TB5, T21	Right Hand
SBB200PLH	1" Tab	35 mm ² Stranded	7.75mm	TB5, T21	Left Hand
SBB200PRH	1" Tab	35 mm ² Stranded	7.75mm	TB5, T21	Right Hand
SBWW6LH	Field-made	50 mm ² Solid	8mm	T21	Left Hand
SBWW6RH	Field-made	50 mm ² Solid	8mm	T21	Right Hand

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte