

Cable to Web of Rail T20 Complete Welder Pair, Power



VLASTNOSTI

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Each part number Includes both right and left hand welders

Includes mold cleaner and flint ignitor

SPECIFIKACE

Bond Terminal Style: W

Table 1/1

Katalogové číslo	Materiál	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBWT20Y301	Graphite, Steel, Thermoplastic	UIC	50 mm ² Concentric	8.9mm	T20
PBWT20X3	Graphite, Steel, Thermoplastic	UIC	50 mm ² Ropelay	9.13mm	T20
PBWT202C	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	1/0 Concentric	9.47mm	T20
PBWT202G	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	2/0 Concentric	10.62mm	T20
PBWT202E	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	1/0 Ropelay	10.87mm	T20

Katalogové číslo	Materiál	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBWT20X401	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	70 mm ² Ropelay	10.92mm	T20
PBWT202J	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	2/0 Ropelay	12.19mm	T20
PBWT202Q	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	4/0 Concentric	13.41mm	T20
PBWT20S6	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	14.5 mm Diameter	14.5mm	T20
PBWT202S	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	4/0 Ropelay	15.49mm	T20
PBWT20X5	Graphite, Steel, Thermoplastic	UIC	95 mm ² Ropelay	15.52mm	T20
PBXLWT20X5	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	15.52mm	T20
PBWT20X7	Graphite, Steel, Thermoplastic	UIC	150 mm ² Ropelay	17.04mm	T20
PBWT203D	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	350 kcmil Concentric	17.3mm	T20
PBWT20X8	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	185 mm ² Ropelay	17.8mm	T20
PBWT202W	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	19.05mm	T20
PBWT202W135	Graphite, Steel, Thermoplastic	135 lb Bethlehem	250 kcmil Ropelay	19.05mm	T20
PBWT202W20AS	Graphite, Steel, Thermoplastic	20 lb ASCE	250 kcmil Ropelay	19.05mm	T20
PBWT20W40AS	Graphite, Steel, Thermoplastic	40 lb ASCE	250 kcmil Ropelay	19.1mm	T20
PBWT203B	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	300 kcmil Ropelay	20.32mm	T20
PBWT203F	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	350 kcmil Ropelay	22.35mm	T20
PBWT20X901	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	240 mm ² Ropelay	23.62mm	T20
PBWT203S	Graphite, Steel, Thermoplastic	85 lb to 141 lb T-Rail Sections	500 kcmil Ropelay	26.42mm	T20

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE