

Cable to Web of Rail T21 Complete Welder Pair, Signal



VLASTNOSTI

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis of 85 to 140 lb. rail

Includes mold cleaner and flint ignitor

SPECIFIKACE

Table 1/2

Katalogové číslo	Article Number	Materiál	Rail Type	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal
SBTBT21R		Ocel, Graphite	UIC	1" Tab	10 mm ² Concentric	4.11mm
SBTBT21B		Ocel, Graphite	85 lb to 141 lb T-Rail Sections	3/4" Tab	3/16" Bondstrand	4.76mm
SBTBT21C	165550	Ocel, Graphite	85 lb to 141 lb T-Rail Sections	1" Tab	3/16" Bondstrand	4.76mm
SBTBT21D		Ocel, Graphite	85 lb to 141 lb T-Rail Sections	1 1/2" Tab	3/16" Bondstrand	4.76mm
SBXST21A		Ocel, Graphite	85 lb to 141 lb T-Rail Sections	3/4" XS	3/16" Bondstrand	4.76mm

Katalogové číslo	Article Number	Materiál	Rail Type	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal
SBTBT21Y		Ocel, Graphite	UIC	1" Tab	16 mm ² Concentric	5.18mm
SBTBT21L		Ocel, Graphite	UIC	1" Tab	22 mm ² Ropelay	6.1mm
SBTBT21X		Ocel, Graphite	85 lb to 141 lb T-Rail Sections	1" Tab	25 mm ² Ropelay	6.6mm
SBTBT21P		Ocel, Graphite	UIC	1" Tab	35 mm ² Concentric	7.75mm
SBTBT21E		Ocel, Graphite	85 lb to 141 lb T-Rail Sections	1" Tab	5/16" Bondstrand	7.94mm

Table 2/2

Katalogové číslo	Article Number	Welder Style
SBTBT21R		T21
SBTBT21B		T21
SBTBT21C	165550	T21
SBTBT21D		T21
SBXST21A		T21
SBTBT21Y		T21
SBTBT21L		T21
SBTBT21X		T21
SBTBT21P		T21
SBTBT21E		T21

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná

instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE