

Earthbridge Jumper



VLASTNOSTI

Designed for use with nVent ERICO Prefabricated Earthbridges

Made to order per specified length (in 50 mm increments only)

SPECIFIKACE

Table 1/2

Katalogové číslo	Materiál	Povrchová úprava	Conductor Type	Conductor Size	Fusing Capacity Equivalency	Lug Size
340970G	Copper, Ocel	Tinned, Electro galvaniz ed	Insulated composite cable	70 mm ² Stranded	70mm ²	10, 12, 16
340870G	Copper, Polyvinylchlorid e	Bare, Tinned	NY Y-0 cable	70 mm ² Stranded		10, 12, 16
340895G	Copper, Polyvinylchlorid e	Bare, Tinned	NY Y-0 cable	95 mm ² Stranded		10, 12, 16

Table 2/2

Katalogové číslo	Length	Length	Rebar Assembly Type	Earthbridge Application	Complies With
340970G	250 - 1700 mm	250mm	Lug	Tunnel	EN IEC® 62561-1 Class H 100kA

Katalogové číslo	Length	Length	Rebar Assembly Type	Earthbridge Application	Complies With
340870G	250 - 1700 mm	250mm	Lug	Tunnel	EN IEC® 62561-1 Class H 100kA
340895G	250 - 1700 mm	250mm	Lug	Tunnel	EN IEC® 62561-1 Class H 100kA

DALŠÍ PODROBNOSTI O PRODUKTU

When ordering, specify the desired length (in 50 mm increments) and lug size. Jumper may also be ordered with no lug on one end.

DB-16-C-70-S-050-C		
DB	Earth Point	DB: 1 hole BT: 2 holes BF: 4 holes LU: M16 lug TA: tape
16	Thread Size	10: M10 12: M12 16: M16 40: Tape 40x5mm 30: Tape 30x4mm
C	Conductor Type	K: Steel Rond C: Y/G Cable T: Steel Bar F: Steel Bar 4mm N: NYY-O Cable H: N2XH-0 Cable
70	Conductor Size	12: D12mm 16: D16mm 30: 30x4mm 40: 40x5mm 50: 50mm ² 70: 70mm ² 95: 95mm ²
S	Conductor Angle	S: 0° P: 90° A: 45°
050	Length (cm)	xxx
x	Termination (option if cable)	SR: Solid Round EP: Earthpoint perpendicular ES: Earthpoint straight TA: Tape of 100mm TP: Tape of 150mm LU: M16 lug
x	Bolts & Washer	- : No Hardware H: With Hardware
C	Packaging	- : by unit (Made-to-Stock) C: 5 pieces (Made-to-Order) G: 25 pieces (Made-to-Order)

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including vinyl chloride, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE