

Joint Bond T7 Complete Welder Pair, Signal



VLASTNOSTI

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail, across the joint

Connection is made within the confines of the splice bar

Includes mold cleaner and flint ignitor

SPECIFIKACE

Rail Type: 85 lb to 141 lb T-Rail Sections

Table 1/1

Katalogové číslo	Materiál	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
SBHFT7E	Ocel, Graphite	Head Free	3/16" Bondstrand	4.76mm	T7
SBHFT7K	Ocel, Graphite	Head Free	5/16" Bondstrand	4.76mm	T7
SBTBT7F	Ocel, Graphite	3/4" Tab	3/16" Bondstrand	4.76mm	T7
SBTBT7G	Ocel, Graphite	1" Tab	3/16" Bondstrand	4.76mm	T7
SBXST7D	Ocel, Graphite	3/4" XS	3/16" Bondstrand	4.76mm	T7
SBTBT7B	Ocel, Graphite	1" Tab	5/16" Bondstrand	7.94mm	T7

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte