

Joint Bond T9 Complete Welder Pair, Power



VLASTNOSTI

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

Includes mold cleaner and flint ignitor

SPECIFIKACE

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: C

Table 1/1

Katalogové číslo	Materiál	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBCT92J	Graphite, Steel, Thermoplastic	2/0 Ropelay	12.19mm	T9
PBCT9S5	Graphite, Steel, Thermoplastic	2/0 Composite	13.36mm	T9
PBCT9S6	Graphite, Steel, Thermoplastic	3/0 Composite	14.53mm	T9
PBCT92S	Graphite, Steel, Thermoplastic	4/0 Ropelay	15.49mm	T9
PBCT92W	Graphite, Steel, Thermoplastic	250 kcmil Ropelay	19.05mm	T9

Katalogové číslo	Materiál	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
PBXLCT92W	Graphite, Steel, Thermoplastic	250 kcmil Ropelay	19.05mm	T9

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE