

nVent ERICO Ericontact Insertion Tool, Manual



VLASTNOSTI

Used to insert single and double nVent ERICO Ericontact Rail Contacts

Packaged in a toolbox for safe and convenient handling

Includes two MDRL (715215) Mandrels for 19 mm nVent ERICO Ericontact

SPECIFIKACE

Table 1/1

Katalogové číslo	Article Number	Applied Force	Operating Pressure	System
HSKE	715345	57kN	630bar	Hydraulic head with manually-operated hydraulic pump

DALŠÍ PODROBNOSTI O PRODUKTU

Kit includes: (2) mandrels for 19 mm nVent ERICO Ericontact rail contact, (1) deburr tool, (1) test gauge, (1) metal case, (1) HSKE pump connected with a high pressure hydraulic hose to the PSKE unit, and (1) manual HSKE.

ERICO ERICONTACT Rail Contact Size	Required Parts	
8 mm	MDRL8ADP (715218) Mandrel Adaptor and MDRL8 (715216) Mandrel	Order separately
13.5 mm	MDRL135ADP (715219) Mandrel Adaptor and MDRL135 (715217) Mandrel	Order separately
19 mm	MDRL (715215) Mandrel	Included
22 mm	PSKECMB (715596) Insertion Head Plate	Order separately

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte