

Plug Bond Track Connector, Signal



VLASTNOSTI

Utilized for attachment of bondstrand or solid copper track wires for track connections, fouling circuits, or bonding around the joint splice bar

Hammered into a 3/8" (9.5 mm) diameter hole drilled through the rail web and driven from the same side the hole was drilled

SPECIFIKACE

Table 1/2

Katalogové číslo	Materiál	Povrchová úprava	Conductor Size	Connector Conductor Size	Length (L)	Diameter 1 (Ø1)
SBPAC3A	Copper Alloy, Cadmium Bronze, Carbon Steel	Electrogalvanized, Tinned, Bare	3/16" Bondstrand	3/16" Bondstrand	120.7mm	4.8 mm


Table 2/2

Katalogové číslo	Diameter 2 (Ø2)	Hloubka (D)
SBPAC3A	10.5 mm	31.75mm

DALŠÍ PODROBNOSTI O PRODUKTU

Plug Bond Grease (T369) recommended when installing.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

⚠ WARNING: This product can expose you to chemicals including cadmium, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE