

Rail Drill Machine, Four-Cycle Gas-Powered



The SBM-V range of petrol/gasoline rail drills are designed for smooth, reliable and powerful drilling operation. It works with products of all sizes, from signalling bond hole applications to fishbolt hole sizes. A wide range of accessories are available, including clamping units, drill cutters, and rail profile and special application templates.

VLASTNOSTI

Compact and easy to use

Quiet 4-stroke 0.83 horsepower (0.62 kW) engine with a 267 rpm spindle speed

Lightweight design

A range of interchangeable templates to suit all common rail profiles

Uses industry-standard drill cutters

Comes standard with COOLTANKASSY (715375) Rail Drill Machine Coolant Tank and SBMTOOLSET (715395) Rail Drill Machine Tool Set for easy maintenance

Includes metal carrying case

SPECIFIKACE

Table 1/1

Katalogové číslo	Article Number	Fuel	Drill Hole Diameter	Width	Unit Weight
SBMV4	715412	No Mix	7 - 24 mm	381 - 457 mm	13 kg

DALŠÍ PODROBNOSTI O PRODUKTU

When ordering a machine, you must also order a rail profile template adapted to the appropriate rail profile and drill-hole position and a clamping device suitable for the rail type and/or clamping method to be selected.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte