

BD Crimp and Drill Tool



CERTIFICATIONS



VLASTNOSTI

For crimping and drilling of braid terminals

Use with FRCB Flat Braid in Coil, Plain Copper and FTCB Flat Braid in Coil, Tinned Copper

Includes guide and drill bit

SPECIFIKACE

Table 1/1

Katalogové číslo	Article Number	Cross Section	Drill Bit Diameter	Screw Diameter	Unit Weight
BD16-8	558640	16mm ²	8.5 mm	8	0.65 kg
BD16	558610	16mm ²	6.5 mm	6	0.65 kg
BD25	558620	25mm ²	11 mm	10	0.68 kg
BD50	558630	50mm ²	12.5 mm	12	0.71 kg

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte