

CABS Module Kit



CERTIFICATIONS



VLASTNOSTI

Modules provide flexibility to select distance between phases and supports

Installs quickly and easily

Halogen free insulators

RoHS compliant

SPECIFIKACE

Typical Application Current Rating:	400 - 4500 A
Max Working Voltage, IEC (Ui):	1000;1500
Povrchová úprava:	Electrogalvanized
Complies With:	IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)
Flammability Rating:	UL® 94V-0
Working Temperature:	-40 to 130 °C

Table 1/2

Katalogové číslo	Article Number	Materiál	Busbars per Phase	Busbar Width	Busbar Thickness	Hloubka (D)
------------------	----------------	----------	-------------------	--------------	------------------	-------------

CABS4-5T-MOD	549370	Ocel, Glass Fibre Reinforced Polyamide	1 - 4	30 - 125 mm	5 mm	39mm
CABS2-10T-MOD	549380	Ocel, Glass Fibre Reinforced Polyamide	1 - 2	30 - 120 mm	10 mm	39mm
CABS3-10T-MOD	549390	Ocel, Glass Fibre Reinforced Polyamide	1 - 3	30 - 120 mm	10 mm	39mm

Table 2/2

Katalogové číslo	Article Number	Width (W)	Unit Weight
CABS4-5T-MOD	549370	75 mm	0.39 kg
CABS2-10T-MOD	549380	75 mm	0.37 kg
CABS3-10T-MOD	549390	100 mm	0.45 kg

DALŠÍ PODROBNOSTI O PRODUKTU

CABS modules must be installed on CABS-APP Aluminium Profile.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE