

CABS Module Kit with Neutral



CERTIFICATIONS



VLASTNOSTI

Modules provide flexibility to select distance between phases and supports

Installs quickly and easily

Halogen free insulators

RoHS compliant

SPECIFIKACE

Typical Application Current Rating:	400 - 4500 A
Max Working Voltage, IEC (Ui):	1000;1500
Povrchová úprava:	Electrogalvanized
Complies With:	IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)
Flammability Rating:	UL® 94V-0
Working Temperature:	-40 to 130 °C

Table 1/2

Katalogové číslo	Article Number	Materiál	Busbars per Phase	Busbar Width	Busbar Thickness	Hloubka (D)
------------------	----------------	----------	-------------------	--------------	------------------	-------------

CABS4-5TN-MOD	549340	Ocel, Glass Fibre Reinforced Polyamide	1 - 4	30 - 125 mm	5 mm	39mm
CABS2-10TN-MOD	549350	Ocel, Glass Fibre Reinforced Polyamide	1 - 2	30 - 120 mm	10 mm	39mm
CABS3-10TN-MOD	549360	Ocel, Glass Fibre Reinforced Polyamide	1 - 3	30 - 120 mm	10 mm	39mm

Table 2/2

Katalogové číslo	Article Number	Width (W)	Unit Weight
CABS4-5TN-MOD	549340	75 mm	0.5 kg
CABS2-10TN-MOD	549350	75 mm	0.48 kg
CABS3-10TN-MOD	549360	100 mm	0.58 kg

DALŠÍ PODROBNOSTI O PRODUKTU

CABS modules must be installed on CABS-APP Aluminium Profile.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE