

EB-12 Earthing and Neutral Busbar



nVent ERIFLEX Connecting, Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, for wind and solar power generation and in data centers.

CERTIFICATIONS



VLASTNOSTI

Use to connect several earthing conductors

Chamfered holes allow for easy connections

Rigid bar

RoHS compliant


SPECIFIKACE

Materiál: Brass

Katalogové číslo	EB12	EB12BLK200
Article Number	568610	568611
Number of Connections	12	12
Conductor Size, IEC	(2) 16 - 35 mm ² Stranded (10) 4 - 16 mm ² Stranded	(2) 16 - 35 mm ² Stranded (10) 4 - 16 mm ² Stranded
Ferrule Conductor Size, IEC	(2) 10 - 35 mm ² (10) 2.5 - 16 mm ²	(2) 10 - 35 mm ² (10) 2.5 - 16 mm ²

Katalogové číslo	EB12	EB12BLK200
Conductor Size, UL	(2) #6 Solid (10) #8 - #6 Solid (2) #6 Stranded (10) #8 - #6 Stranded	(2) #6 Solid (10) #8 - #6 Solid (2) #6 Stranded (10) #8 - #6 Stranded
Max Current Rating	250A	250A
Hloubka (D)	6mm	6mm
Height (H)	13 mm	13 mm
Width (W)	120 mm	120 mm
A	105 mm	105 mm
B	9 mm	9 mm
Unit Weight	0.07 kg	0.07 kg
Complies With	IEC® 61439.1	IEC® 61439.1

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE