

nVent ERIFLEX Flexibar Advanced Kit



VLASTNOSTI

Connects busbar to fixed switchgear

Kit includes preformed nVent ERIFLEX Flexibar Advanced with punched ends and end covers

Kit can be used in three configurations

Insulated by high-resistance, halogen free, flame retardant and low smoke material with less than 20% contact with conductor for high flexibility

Tinned copper allows for copper or aluminum conductor connections

RoHS compliant

SPECIFIKACE

Halogen Free Rating:	UL® 2885;IEC® 60754-1;IEC® 62821-1
Smoke, Toxicity and Acidity Rating:	IEC® 60754-2
Low Smoke Rating:	IEC® 61034-2;ISO 5659-2;UL® 2885
UV Resistance Rating:	UL® 854;UL® 2556
Flammability Rating:	UL® 94V-0

Table 1/1

Katalogové číslo	Article Number	Typical Application Current Rating	Typ	Unit Weight
FLXADVKIT250AT	534800	250 A	Three Phase	0.76 kg
FLXADVKIT250ATN	534805	250 A	Three Phase with Neutral	0.98 kg

Katalogové číslo	Article Number	Typical Application Current Rating	Typ	Unit Weight
FLXADVKIT630AT	534810	630 A	Three Phase	2.1 kg
FLXADVKIT630ATN	534815	630 A	Three Phase with Neutral	3.1 kg

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE