

nVent ERIFLEX Flexidrill Drill Guide



CERTIFICATIONS



VLASTNOSTI

Guide for drilling holes into nVent ERIFLEX Flexibar, PBC Braided Power Shunts and PPS Presswelded Power Shunts

Includes dies for multiple diameters

Adjustable guides allow for multiple hole center to hole center distances

RoHS compliant

SPECIFIKACE

Table 1/2

Katalogové číslo	Article Number	Materiál	Die Hole Size	Hloubka	Height	Width
FLEXIDRILLR	558600	Ocel	6.5 mm, 8.5 mm, 10.5 mm, 12.5 mm	300mm	150 mm	250 mm

Table 2/2

Katalogové číslo	Article Number	Unit Weight
FLEXIDRILLR	558600	9.5 kg

DALŠÍ PODROBNOSTI O PRODUKTU

Do not use with nVent ERIFLEX Flexibar Summum.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE