

RRCB Round Braid in Coil, Plain Copper



CERTIFICATIONS



VLASTNOSTI

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

SPECIFIKACE

Materiál: Copper

Table 1/2

Katalogové číslo	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
RRCB15-10	557420	75A	10mm ²	560	0.15mm	25m
RRCB15-16	557430	120A	16mm ²	900	0.15mm	25m
RRCB15-25	557440	150A	25mm ²	1416	0.15mm	25m
RRCB15-30	557450	180A	30mm ²	1680	0.15mm	25m

Katalogové číslo	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
RRCB15-50	557460	250A	50mm ²	2820	0.15mm	25m
RRCB15-6	557400	45A	6mm ²	352	0.15mm	25m
RRCB15-75	557470	300A	75mm ²	4236	0.15mm	25m

Table 2/2

Katalogové číslo	Article Number	Diameter	Unit Weight
RRCB15-10	557420	5 mm	0.1 kg
RRCB15-16	557430	6 mm	0.16 kg
RRCB15-25	557440	8 mm	0.25 kg
RRCB15-30	557450	9 mm	0.3 kg
RRCB15-50	557460	11 mm	0.5 kg
RRCB15-6	557400	4 mm	0.06 kg
RRCB15-75	557470	14 mm	0.75 kg

DALŠÍ PODROBNOSTI O PRODUKTU

Unit weight is per meter (3.28').

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE