

Nerezová ocel, Jednolitá samostatne stojící, SSFS



This single-door enclosure provides industry-leading protection for systems incorporating large components or complex mounting configurations in highly corrosive environments. The addition of 19-in. rack-mounting accessories makes these enclosures ideal for providing rugged protection for sensitive rack-mounted components in harsh industrial environments. The enclosure is typically used in food-processing plants, pharmaceutical manufacturing facilities, petrochemical plants and waste-water treatment facilities.

PRŮMYSLOVÉ NORMY

IEC EN 60529, IP66

IEC EN 50102, IK10

IEC EN 62208;

UL 508A Listed;

Type 4, 4X, 12 File No. E61997

NEMA Type 4, 4X, 12

VLASTNOSTI

Two-door enclosures are provided with a removable centerpost for easy mounting plate installation

Seamless foam-in-place polyurethane gasket assures a water-tight and dust-tight seal

High-impact thermoplastic data pocket provided with each enclosure

Base plinth 100 mm included, with front and rear removable cover for easy cable entry

External surface body and door brushed finish grain 240, Ra less than or equal to 0,8 um, smooth internal surface (2B)

Heavy-duty three-point latching mechanism operated by Type 316L stainless steel PowerGlide padlocking handle

Seams continuously welded and ground smooth

Body grounding, studs door and body

Bottom gland plates, 3,0 mm removable from inside, with grounding stud

Door opening angle 100 degrees

SPECIFIKACE

Tloušťka:	2.5mm
Povrchová úprava:	Leštěná
Montážní deska v ceně:	No
Gland Plate Included:	Yes

Table 1/1

Katalogové číslo	Výška	Šířka	Hloubka	Materiál	Výška montážní desky	Šířka montážní desky
A18104SS6FS	1800mm	1000mm	400mm	Nerezová Ocel 316L	1595mm	897mm
A18104SSFS	1800mm	1000mm	400mm	Stainless Steel 304	1595mm	897mm
A18106SSFS	1800mm	1000mm	600mm	Stainless Steel 304	1595mm	897mm
A18124SSFSD	1800mm	1200mm	400mm	Stainless Steel 304	1595mm	1097mm
A18126SSFSD	1800mm	1200mm	600mm	Stainless Steel 304	1595mm	1097mm
A1864SSFS	1800mm	600mm	400mm	Stainless Steel 304	1595mm	497mm
A1866SSFS	1800mm	600mm	600mm	Stainless Steel 304	1595mm	497mm
A1884SSFS	1800mm	800mm	400mm	Stainless Steel 304	1595mm	697mm
A1886SSFS	1800mm	800mm	600mm	Stainless Steel 304	1595mm	897mm
A20106SSFS	2000mm	1000mm	600mm	Stainless Steel 304	1795mm	897mm
A20108SS6FSDA	2000mm	1000mm	800mm	Nerezová Ocel 316L	1795mm	897mm
A20108SSFSDA	2000mm	1000mm	800mm	Stainless Steel 304	1795mm	897mm
A20126SSFSD	2000mm	1200mm	600mm	Stainless Steel 304	1795mm	1097mm
A20128SS6FSDA D	2000mm	1200mm	800mm	Nerezová Ocel 316L	1795mm	1097mm
A20128SSFSD	2000mm	1200mm	800mm	Stainless Steel 304	1795mm	1097mm
A20128SSFSDAD	2000mm	1200mm	800mm	Stainless Steel 304	1795mm	1097mm

Katalogové číslo	Výška	Šířka	Hloubka	Materiál	Výška montážní desky	Šířka montážní desky
A20168SS6FSDA D	2000mm	1560mm	800mm	Nerezová Ocel 316L	1795mm	1463mm
A20168SSFSD	2000mm	1560mm	800mm	Stainless Steel 304	1795mm	1463mm
A20168SSFSDAD	2000mm	1560mm	800mm	Stainless Steel 304	1795mm	1463mm
A2066SSFS	2000mm	600mm	600mm	Stainless Steel 304	1795mm	497mm
A2068SSFS	2000mm	600mm	800mm	Stainless Steel 304	1795mm	497mm
A2086SSFS	2000mm	800mm	600mm	Stainless Steel 304	1795mm	697mm
A2088SS6FS	2000mm	800mm	800mm	Nerezová Ocel 316L	1795mm	697mm
A2088SS6FSDA	2000mm	800mm	800mm	Nerezová Ocel 316L	1795mm	697mm
A2088SSFS	2000mm	800mm	800mm	Stainless Steel 304	1795mm	697mm
A2088SSFSDA	2000mm	800mm	800mm	Stainless Steel 304	1795mm	697mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE