

CS480 Swivel Base Internal



CS480 Swivel Base Internal allows the entire suspension system to rotate at the point of attachment on a horizontal surface. Arm can be rotated or turned 340 degrees. Base mounting hardware is hidden. Maintenance-free bearings.

PRŮMYSLOVÉ NORMY

IEC 60529, IP66

VLASTNOSTI

Base can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket is included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFIKACE

Table 1/1

Katalogové číslo	Výška	Šířka	Hloubka	Materiál	Povrchová úprava	Rychlé odeslání
CCSS48BBRI	110mm	116mm	116mm	Stainless Steel 304	Leštěná	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE