

Heavy-Duty Swing-Out Rack Frame



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

VLASTNOSTI

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Spring-loaded pivot post makes installation easy

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

Mounting holes accommodate either English or metric cage nuts, which are ordered separately

Swing-Out Rack Frame assemblies are supplied with mounting supports

Hinges that provide 170-degree rotation are optional

RAL 7035 textured light-gray polyester powder paint

SPECIFIKACE

Tloušťka:	2.66mm
Barva:	Light Gray
Povrchová úprava:	Strukturovaný Práškový
Kód barvy:	RAL 7035

Table 1/1

Katalogové číslo	Materiál	Fits Frame Width	Rack Units	Rychlé odeslání
PSF76	Ocelový Plech	600mm	10U	Ne
PSF146	Ocelový Plech	600mm	25U	Ne
PSF148	Ocelový Plech	800mm	25U	Ne
PSF78	Ocelový Plech	800mm	10U	Ne
PSF168	Ocelový Plech	800mm	30U	Ne
PSF186	Ocelový Plech	600mm	34U	Ne
PSF188	Ocelový Plech	800mm	34U	Ne
PSF206	Ocelový Plech	600mm	39U	Ne
PSF77	Ocelový Plech	700mm	10U	Ne
PSF207	Ocelový Plech	700mm	39U	Ne
PSF208	Ocelový Plech	800mm	39U	Ne
PSF226	Ocelový Plech	600mm	43U	Ne
PSF227	Ocelový Plech	700mm	43U	Ne
PSF228	Ocelový Plech	800mm	43U	Ne
PSF166	Ocelový Plech	600mm	30U	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE