

Kolenová spojka HMI, lehká, S1MFEC



Suspend 180-Max Flange Elbow Coupling attaches directly to the enclosure for applications where a vertical tube is not required. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The flange elbow coupling has a safety stop and maintenance-free bearings.

VLASTNOSTI

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Suspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

SPECIFIKACE

Materiál: Hliník
Povrchová úprava: Strukturovaný Práškový

Table 1/1

Katalogové číslo	Výška	Šířka	Hloubka	Barva	Kód barvy	Rychlé odeslání
S1MFECG	138mm	125mm	124mm	Light Gray	RAL 7035	Ne
S1MFEC	138mm	195mm	125mm	Jet Black	RAL 9005	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE