

# Vertikální panelová spojka, lehká, S1MPCV



Suspend 180-Max Vertical Panel Coupling mounts a vertical tube to the back of an enclosure or screen using Video Electronics Standards Association (VESA) mounting. The coupling has mounting holes drilled for standard VESA 75 and 100 flange sizes. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The vertical panel coupling has a safety stop and maintenance-free bearings.

## VLASTNOSTI

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Suspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

## SPECIFIKACE

**Materiál:** Hliník  
**Povrchová úprava:** Strukturovaný Práškový

Table 1/1

| Katalogové číslo | Výška | Šířka | Hloubka | Barva      | Kód barvy | Tloušťka |
|------------------|-------|-------|---------|------------|-----------|----------|
| S1MPCVG          | 185mm | 120mm | 140mm   | Light Gray | RAL 7035  | 5.5mm    |
| S1MPCV           | 256mm | 140mm | 120mm   | Jet Black  | RAL 9005  | 5.5mm    |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**