

Konzola otocné základny, S2MRB



Suspend 281-Max Rotary Base allows the entire suspension system to rotate at the point of attachment on a horizontal surface. Arm can be rotated or turned 300 degrees. Includes safety stop and maintenance-free bearing.

VLASTNOSTI

Set screws and gasket are included

Surface mounting fasteners are not provided

Assembled Suspend 281 HMI Arm System has a max weight load of 281 lb. (127.7 kg)

SPECIFIKACE

Table 1/1						
Katalogové číslo	Výška	Šířka	Hloubka	Materiál	Povrchová úprava	Barva
S2MRB	167mm	125mm	125mm	Hliník	Strukturovaný Práškový	Jet Black

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE