

Profil otocných ramen, S2MT



Suspend 281-Max tubes provide structural integrity and act as conduit for equipment wiring. Tubes attach to system components with 6 set screws on each end of the tube. Set screws allow for easy adjustment and leveling of the system. Set screws are provided with thread sealer providing secure connections.

VLASTNOSTI

Set screws are provided with system couplings, not the tubes

Tubes 750 mm and longer include drilling template to assist with drilling and tapping the holes when the tube is cut to length

Assembled Suspend 281 HMI Arm System has a max weight load of 281 lb. (127.7 kg)

SPECIFIKACE

Materiál: Hliník
Povrchová úprava: Anodized

Table 1/1

Katalogové číslo	Výška	Šířka	Hloubka	Tloušťka	Rychlé odeslání
S2MT1000	90mm	70mm	1000mm	6mm	Ne
S2MT1250	90mm	70mm	1250mm	6mm	Ne
S2MT1500	90mm	70mm	1500mm	6mm	Ne
S2MT1750	90mm	70mm	1750mm	6mm	Ne
S2MT2000	90mm	70mm	2000mm	6mm	Ne
S2MT250	90mm	70mm	250mm	6mm	Ne
S2MT500	90mm	70mm	500mm	6mm	Ne
S2MT750	90mm	70mm	750mm	6mm	Ne

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE