

Universal busbar supports | Power Distribution, EUBS-PD



This busbar support, EUBS, is available for one, two, or three bars up to 120 x 10 mm. The support can be mounted either at the top or bottom of the enclosure. It is available off the shelf and tested according to IEC 61439. This support is required when a high level of mounting flexibility is required.

VLASTNOSTI

Popis: Busbar support up to 4500A to be mounted horizontally or vertically. Mounts directly to the enclosure frame or with help of CLPF profiles. Available in one/two/three bars per phase for bar thickness 10 mm, and width from 30 to 120 mm.

Provozní teplota: -40°C up to 130°C.

Materiál: Reinforced polyamide and steel. Halogen free.

Dodávka: Busbar support with mounting material.

SPECIFIKACE

Table 1/1						
Katalogové číslo	Busbar Thickness	Busbars per Phase	Busbar Width	Materiál	Povrchová úprava	Barva
EUBS310TN	10mm min	3Ph min	30 – 125mm	Ocel, Polyamide	Plated	Black
EUBS110TN	10mm min	1Ph min	30 – 125mm	Ocel, Polyamide	Plated	Black
EUBS210TN	10mm min	2Ph min	30 – 125mm	Ocel, Polyamide	Plated	Black

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte