


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded, Front Handle

Power Utilities

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICATIONS



VLASTNOSTI

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded) and includes handles

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

IP 20, in accordance with IEC 60529

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Gasket Type
24567-474	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24567-473	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24567-472	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24567-174	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24567-173	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24567-172	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile

Table 2/3

Katalogové číslo	Shock and Vibration Tolerance	Rukojeť v ceně	Mounting	Complies With	EMC Shielding	Product Type
24567-474	5 g (force)	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24567-473	5 g (force)	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24567-472	5 g (force)	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24567-174	5 g (force)	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24567-173	5 g (force)	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24567-172	5 g (force)	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis

Table 3/3

Katalogové číslo	Rack Width	Static Load
24567-474	84 HP	15 kgf
24567-473	84 HP	15 kgf

Katalogové číslo	Rack Width	Static Load
24567-472	84 HP	15 kgf
24567-174	84 HP	15 kgf
24567-173	84 HP	15 kgf
24567-172	84 HP	15 kgf

DALŠÍ PODROBNOSTI O PRODUKTU

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE