

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Power Utilities

Non-EMC shielded subrack for backplane mounting, light version.



CERTIFICATIONS



VLASTNOSTI

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	Rukojeť v ceně
24564-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24564-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	No
24564-431	6 U	175 mm	1	Backplane	160 mm	No
24564-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24564-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	No
24564-131	3 U	175 mm	1	Backplane	160 mm	No

Table 2/2

Katalogové číslo	Mounting	Complies With	EMC Shielding	Product Type	Rack Width	Static Load
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf

DALŠÍ PODROBNOSTI O PRODUKTU

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte