

EuropacPRO 19" Subrack Kit for Backplane, Shielded, CompactPCI

Power Utilities

EMC Shielded subrack for backplane mounting, for CPCI application.

CERTIFICATIONS



VLASTNOSTI

Subrack with side panel type F ("flexible") for CompactPCI plug-in units with high insertion and withdrawal forces

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, -102, -103, -104, IEEE 1101.1, IEEE 1101.10/11

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Supplied as space-saving flat-pack

IP 20, in accordance with IEC 60529

Horizontal rail type "Heavy"

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Hloubka	Rear I/O	Množství v balení	For Mounting	Board Depth
24563-157	3 U	275 mm	Yes	1	Backplane	80 mm, 160 mm

Katalogové číslo	Rack Height	Hloubka	Rear I/O	Množství v balení	For Mounting	Board Depth
24563-152	3 U	235 mm		1	Backplane	160 mm
24563-452	6 U	235 mm		1	Backplane	160 mm
24563-457	6 U	275 mm	Yes	1	Backplane	80 mm, 160 mm

Table 2/3

Katalogové číslo	EMC Gasket Type	Rukojeť v ceně	Mounting	Complies With	EMC Shielding	Product Type
24563-157	Textile	No	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	Yes	Subrack/Chassis
24563-152	Textile	No	Rack	IEC 60297-3-103, IEEE 1101.10	Yes	Subrack/Chassis
24563-452	Textile	No	Rack	IEC 60297-3-103, IEEE 1101.10	Yes	Subrack/Chassis
24563-457	Textile	No	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	Yes	Subrack/Chassis

Table 3/3

Katalogové číslo	Rack Width	Static Load
24563-157	84 HP	11 kgf
24563-152	84 HP	11 kgf
24563-452	84 HP	11 kgf
24563-457	84 HP	11 kgf

DALŠÍ PODROBNOSTI O PRODUKTU

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE