

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Power Utilities

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



CERTIFICATIONS



VLASTNOSTI

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Hloubka	Množství v balení	For Mounting	Board Depth	EMC Gasket Type
24563-191	3 U	175 mm	1	DIN Connector	160 mm	Stainless Steel
24563-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Stainless Steel
24563-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Stainless Steel
24563-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel
24563-491	6 U	175 mm	1	DIN Connector	160 mm	Stainless Steel
24563-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Stainless Steel
24563-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Stainless Steel
24563-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel

Table 2/3

Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-191	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-192	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-193	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-194	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-491	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-492	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-493	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24563-494	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Katalogové číslo	Static Load
24563-191	11 kgf
24563-192	11 kgf
24563-193	11 kgf
24563-194	11 kgf
24563-491	11 kgf
24563-492	11 kgf
24563-493	11 kgf
24563-494	11 kgf

DALŠÍ PODROBNOSTI O PRODUKTU

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE