

EuropacPRO 19" Subrack Kit for Railway, Shielded, SNCF

Power Utilities

Subrack for Railway applications, conform to SNCF Standard.



CERTIFICATIONS



VLASTNOSTI

SNCF listed, EuropacPRO-fer, tested to NF F 61-005 and NF F 60-002

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

Lateral support bars to NFF standard facilitate insertion of subrack into the (cabinet) frame. The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Rack Width	Množství v balení	For Mounting	Board Depth	Shock and Vibration Tolerance
21500-071	6 U	36 HP	1	Backplane	220 mm	5 g (force)
21500-068	3 U	36 HP	1	Backplane	220 mm	5 g (force)
21500-030	3 U	84 HP	1	Backplane	220 mm	5 g (force)
21500-028	6 U	84 HP	1	Backplane	220 mm	5 g (force)

Table 2/3

Katalogové číslo	Rukojeť v ceně	Mounting	Complies With	Hloubka	EMC Shielding	Product Type
21500-071	Yes	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Yes	Subrack/Chassis
21500-068	Yes	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Yes	Subrack/Chassis
21500-030	Yes	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Yes	Subrack/Chassis
21500-028	Yes	Rack	IEC 60297-3-103, SNCF NFF 61005, SNCF NFF 60002	320 mm	Yes	Subrack/Chassis

Table 3/3

Katalogové číslo	Static Load	Certifications
21500-071	15 kgf	RoHS
21500-068	15 kgf	RoHS
21500-030	15 kgf	RoHS, SNCF

Katalogové číslo	Static Load	Certifications
21500-028	15 kgf	RoHS, SNCF

DALŠÍ PODROBNOSTI O PRODUKTU

Fer = ferroviaire = French Railways, 1 T = 4 HP = 20.32 mm.

Receptacle/mounting frame for subracks, stainless steel, 9 T or 21 T on request.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE