

MultipacPRO 19" Chassis, Steel, AlZn, Plain Top and Base

Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version is produced from sheet metal, Al-Zn coated and have plain top and bottom covers.

CERTIFICATIONS



VLASTNOSTI

Steel (AlZn coated) with Al extrusion front panel

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

EMC shielding: Approx. 20dB(A) at 2GHz without shielding material. >40dB(A) at 1Ghz with addition of stainless steel gasket between front panel and case body

Internal and external dimensions in accordance with: IEC 60297-3-101

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Usable Width	Mounting	Complies With	EMC Shielding
20860-122	1 U	340 mm	447 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-120	1 U	220 mm	447 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-121	1 U	280 mm	447 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-127	2 U	340 mm	447 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-126	2 U	280 mm	447 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Katalogové číslo	Produktová řada	Product Type	Typ
20860-122	MultipacPRO	Subrack/Chassis	Solid
20860-120	MultipacPRO	Subrack/Chassis	Solid
20860-121	MultipacPRO	Subrack/Chassis	Solid
20860-127	MultipacPRO	Subrack/Chassis	Solid
20860-126	MultipacPRO	Subrack/Chassis	Solid

DALŠÍ PODROBNOSTI O PRODUKTU

Please order front handles separately.

Telescopic slides cannot be used.

Further versions with steel front panel (pizza box) available on request.

Standardised internal mounting kits cannot be used.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit

selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE