

Novastar Cabinet With Glazed Door and Rear Panel

Power Utilities



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICATIONS



VLASTNOSTI

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Frame Color	Výška	Frame Color Code	Cladding Material	Šířka
------------------	-------------	-------------	-------	------------------	-------------------	-------

15230-019	12 U	Black Grey	589 mm	RAL 7021	Ocel	553 mm
16230-019	12 U	Black Grey	589 mm	RAL 7021	Ocel	553 mm
15230-020	16 U	Black Grey	767 mm	RAL 7021	Ocel	553 mm
16230-020	16 U	Black Grey	767 mm	RAL 7021	Ocel	553 mm
15230-021	20 U	Black Grey	945 mm	RAL 7021	Ocel	553 mm
16230-021	20 U	Black Grey	945 mm	RAL 7021	Ocel	553 mm
15230-022	38 U	Black Grey	1745 mm	RAL 7021	Ocel	553 mm
15230-023	38 U	Black Grey	1745 mm	RAL 7021	Ocel	553 mm
16230-022	38 U	Black Grey	1745 mm	RAL 7021	Ocel	553 mm
16230-023	38 U	Black Grey	1745 mm	RAL 7021	Ocel	553 mm
15230-024	43 U	Black Grey	1967 mm	RAL 7021	Ocel	553 mm
15230-025	43 U	Black Grey	1967 mm	RAL 7021	Ocel	553 mm
16230-024	43 U	Black Grey	1967 mm	RAL 7021	Ocel	553 mm
16230-025	43 U	Black Grey	1967 mm	RAL 7021	Ocel	553 mm

Table 2/3

Katalogové číslo	Cladding Color	Hloubka	Static Load	Cladding Color Code	Complies With	Frame Material
15230-019	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Hliník
16230-019	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Hliník
15230-020	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Hliník

Katalogové číslo	Cladding Color	Hloubka	Static Load	Cladding Color Code	Complies With	Frame Material
16230-020	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Hliník
15230-021	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Hliník
16230-021	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Hliník
15230-022	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Hliník
15230-023	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Hliník
16230-022	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Hliník
16230-023	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Hliník
15230-024	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Hliník
15230-025	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Hliník
16230-024	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Hliník
16230-025	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Hliník

Table 3/3

Katalogové číslo	Product Type	Stupeň krytí
15230-019	Cabinet	IP20
16230-019	Cabinet	IP20
15230-020	Cabinet	IP20
16230-020	Cabinet	IP20
15230-021	Cabinet	IP20
16230-021	Cabinet	IP20

Katalogové číslo	Product Type	Stupeň krytí
15230-022	Cabinet	IP20
15230-023	Cabinet	IP20
16230-022	Cabinet	IP20
16230-023	Cabinet	IP20
15230-024	Cabinet	IP20
15230-025	Cabinet	IP20
16230-024	Cabinet	IP20
16230-025	Cabinet	IP20

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE