


Novastar Raised Top Cover

Power Utilities



Raised top cover for better ventilation and heat escape.
Novastar raised top cover is robust and not dismountable from the outside.

CERTIFICATIONS



VLASTNOSTI

Raised Top cover (31 mm) with all-round air gap of 10 mm

Top cover attached from the inside (no screws on the outside)

Suitable for placing heavy parts on the top cover

Incl. grounding

SPECIFIKACE

Table 1/1						
Katalogové číslo	Hloubka	Barva	Kód barvy	Product Type	Typ	Šířka
25230-010	500 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-046	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-045	900 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-012	800 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-011	600 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm

DALŠÍ PODROBNOSTI O PRODUKTU

Please order lifting eye separately if required.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte