

RackPower Basic PDU, RB0xxx, 100-240 VAC, 1-phase

Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

VLASTNOSTI

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFIKACE

Table 1/2

Katalogové číslo	Product Type	Typ zásuvky	Barva	Length	Napětí střídavé	Hloubka
RB0322	Socket Strip	IEC C13, IEC C19	Black	817 mm	230 V	53 mm

Table 2/2

Katalogové číslo	Šířka
RB0322	52 mm

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE