

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Power Utilities

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

VLASTNOSTI

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Výška	Frame Color	Šířka	Frame Color Code	Cladding Material
10630-034	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Ocel
10630-033	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Ocel
10630-035	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Ocel
10630-036	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Ocel

Table 2/3

Katalogové číslo	Hloubka	Cladding Color	Cladding Color Code	Complies With	Frame Material	Product Type
------------------	---------	----------------	---------------------	---------------	----------------	--------------

10630-034	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Ocel	Cabinet
10630-033	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Ocel	Cabinet
10630-035	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Ocel	Cabinet
10630-036	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Ocel	Cabinet

Table 3/3

Katalogové číslo	Static Load
10630-034	400 kgf
10630-033	400 kgf
10630-035	400 kgf
10630-036	400 kgf

DALŠÍ PODROBNOSTI O PRODUKTU

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE