

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Power Utilities

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

VLASTNOSTI

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

SPECIFIKACE

Table 1/3

Katalogové číslo	Rack Height	Výška	Šířka	Barva	Kód barvy	Complies With
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Katalogové číslo	Povrchová úprava	Locking Type	Materiál	Product Type	Stupeň krytí	Typ
21630-823	Strukturovaný Práškový	3-Point Locking, Electronic	Ocel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Strukturovaný Práškový	3-Point Locking, Electronic	Ocel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-820	Strukturovaný Práškový	3-Point Locking, Electronic	Ocel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Strukturovaný Práškový	3-Point Locking, Electronic	Ocel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Strukturovaný Práškový	3-Point Locking, Electronic	Ocel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Strukturovaný Práškový	3-Point Locking, Electronic	Ocel	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Katalogové číslo	Works With
21630-823	Varistar CP
21630-822	Varistar CP
21630-820	Varistar CP
21630-825	Varistar CP
21630-824	Varistar CP
21630-821	Varistar CP

DALŠÍ PODROBNOSTI O PRODUKTU

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE