

Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking

Power Utilities

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

VLASTNOSTI

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Výška	Šířka	Barva	Kód barvy	Complies With
21630-876	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-877	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-878	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-879	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-880	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-881	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-882	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Katalogové číslo	Rack Height	Výška	Šířka	Barva	Kód barvy	Complies With
21630-883	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Table 2/2

Katalogové číslo	Locking Type	Materiál	Product Type	Stupeň krytí	Typ	Works With
21630-876	4-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-877	4-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-878	4-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-879	4-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-880	4-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-881	4-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-882	5-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-883	5-Point Locking	Ocel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

DALŠÍ PODROBNOSTI O PRODUKTU

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE