

Varistar CP Seismic Base/Plinth

Power Utilities

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

VLASTNOSTI

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

SPECIFIKACE

Table 1/2

Katalogové číslo	Šířka	Hloubka	Barva	Kód barvy	Complies With	Výška
21630-110	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-111	600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-112	600 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-113	600 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-114	800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-115	800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-117	800 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm

Katalogové číslo	Šířka	Hloubka	Barva	Kód barvy	Complies With	Výška
21630-116	800 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	800 mm

Table 2/2

Katalogové číslo	Materiál	Product Type	Static Load	Typ	Works With
21630-110	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-111	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-112	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-113	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-114	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-115	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-117	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-116	Ocel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP

DALŠÍ PODROBNOSTI O PRODUKTU

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE