

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC

Power Utilities

Cabinet with IP 55 and EMC compliance for extreme seismic environments tested to Bellcore zone 4 with a dynamic load-carrying capacity of 500 kg. Customised solutions with higher loading are available. The cabinet is widely used in ICT applications in earthquake prone areas, Construction and Shipping Facilities, Airports, Railways and many more.

Other dimensions and versions can be configured on the Online Configurator

VLASTNOSTI

Earthquake secure up to Bellcore Zone 4, tested with 500 KGs per Telcordia GR-63 Core, NEBS Certified

Static load-carrying capacity 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket

SPECIFIKACE

Table 1/3

Katalogové číslo	Frame Material	Rack Height	Výška	Šířka	Hloubka	Static Load
10630-048	Ocel	42 U	2000 mm	600 mm	800 mm	1600 kgf

Table 2/3

Katalogové číslo	Stupeň krytí	Complies With	Barva	Kód barvy	Materiál	Shock and Vibration Tolerance

10630-048	IP55	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3, IEC 61587-1, IEC 61587-2, EN 45545-2	Black Grey	RAL 7021	Ocel	5 g (force)
-----------	------	--	------------	----------	------	-------------

Table 3/3

Katalogové číslo	Works With
10630-048	Varistar CP

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE