

Varistar CP Steel Door, Perforated With 3-Point Locking

Power Utilities

Varistar CP perforated steel door 3-point locking for IP 20 applications.

VLASTNOSTI

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Výška	Šířka	Barva	Kód barvy	Complies With
21630-098	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-099	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-100	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-101	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-102	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-103	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-424	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Katalogové číslo	Rack Height	Výška	Šířka	Barva	Kód barvy	Complies With
21630-425	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-426	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-427	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-428	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-429	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-430	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-431	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Katalogové číslo	Locking Type	Product Type	Stupeň krytí	Typ	Works With
21630-098	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-099	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-100	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-101	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-102	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-103	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-424	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-425	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-426	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-427	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

Katalogové číslo	Locking Type	Product Type	Stupeň krytí	Typ	Works With
21630-428	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-429	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-430	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-431	3-Point Locking	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

DALŠÍ PODROBNOSTI O PRODUKTU

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE